



Ortronics fiber adapter panel allows for flexibility and expansion with an industry accepted style. The adapter panel snaps in for installation and can be removed easily for future changes. The adapter panel is silkscreened for easy port identification.

Features & Benefits

- Up to 72 LC fibers per RU
- Made of durable polycarbonate
- 6, 8, 12 & 24 port panels
- Available in, LC, SC, ST and blank styles
- Zirconia ceramic sleeves for optimal performance
- Color options available

Specifications

General Info

Product Line	Ortronics	Color	Blue
UPC Number	662875593799	Country Of Origin	Mexico
Application Sector	Commercial	Standard	RoHS compliant. Meets or exceeds TIA/EIA-568-C.3 requirements.
Warranty Type	5-Year	Type	Adapter Panel

Dimensions

Product Width US	5.12 in	Product Depth US	1.15 in
Product Height US	1.19 in		

Additional Information

Product Environmental Profile	Yes
-------------------------------	-----

Technical Information

Fiber Optic Cable Type	OS2	Number of Ports	12
Simplex/Duplex	Duplex	Single/Multimode	Single-Mode
Number of Fibers	12 Fibers	Fiber Type	Single-Mode
Form Factor	LC Duplex		