




the
radiant[®]
collection

Dimmers & Switches




TRU-UNIVERSAL DIMMER | RH703PTUW

The simplest solution to every dimming need, this dimmer self-calibrates to work with dimmable lighting types and loads (except 0-10V). White LED enables easy location in the dark.

MULTI-LOCATION MASTER DIMMER | HCL453PMMW

This CFL/LED multi-location dimmer allows dimming from multiple locations.



SINGLE-POLE COMBINATION SWITCH | RCD11W

The clean look of radiant hits home in this handsome combination switch. Two single pole switches tuck neatly into a single wall plate, delivering convenience without the clutter.

SINGLE-POLE SWITCH WITH LOCATOR LIGHT | TM870WSL

Conveniently locate your switch in the dark with the small, subtle locator light that illuminates when switched off.

Outlets



TAMPER-RESISTANT OUTLET | 885TRW
Discreetly prevents insertion of foreign objects with patented “invisi-shutters.”

TAMPER-RESISTANT SELF-TEST GFCI OUTLET | 1597TRW
Self-tests at the industry-leading rate of every 3 seconds to offer superior ground-fault protection.

TAMPER-RESISTANT SELF-TEST GFCI USB TYPE-A/OUTLET | 1597TRUSBACW
A one-of-a-kind solution featuring superior ground-fault protection and convenient built-in charging in a single outlet.



SINGLE POLE/3-WAY SWITCH/TAMPER-RESISTANT OUTLET COMBINATION | RCD38TRW
Fit two devices neatly into the footprint of one with this combination single-pole/3-way switch and tamper-resistant outlet.

WEATHER-RESISTANT OUTLET | 885TRWRW
Perfect for a home’s outdoor spaces, this outlet is made to work, rain or shine.

USB Charging Solutions



WIRELESS CHARGER | RWC826USBWCCV2

Instantly provides a revolutionary new way to charge your phone using Qi charging technology and cuts the cord for your devices — finally, they are truly wireless.

TAMPER-RESISTANT ULTRA-FAST PLUS POWER DELIVERY USB TYPE-C/OUTLET | R26USBPDW

Combines our industry-leading 6 amps of power with advanced Power Delivery for a charge that is up to 2x faster.



TAMPER-RESISTANT ULTRA-FAST USB TYPE-A/OUTLET | R26USBAC6W

With an industry-leading 6 amps of power, this USB outlet provides a quicker charge for phones, tablets and other devices, meaning no more low battery anxiety.

QUAD USB CHARGER | TM8USB4WCC6

With 4.2 amps of charging capacity, the quad USB gives users the power to charge up to four devices simultaneously without the need for bulky adapters.

Night Lights



FULL LED NIGHT LIGHT | NTLFULLW
Energy-efficient soft-glowLED features five adjustable brightness levels and optional louver for greater control.
Shown with included optional louver.




NIGHT LIGHT WITH TAMPER-RESISTANT OUTLET | NTL885TRW
This seamlessly integrated night light features five adjustable brightness levels, an optional louver for greater light control and a hidden sensor that turns light on in the dark, off in daylight.

COMBINATION TAMPER-RESISTANT SELF-TEST NIGHT LIGHT/GFCI | 1597NTLW
For superior safety, this outlet offers all the protection of tamper-resistance and GFCI functionality, with an included night light for added convenience.

Smart Lighting



Create scenes, set schedules and control lights with the Legrand Smart Lights, Wi-Fi app.



Manage lights and power, from anywhere, with the Legrand Home + Control app.



radiant[®] WITH Netatmo



SMART SWITCH WITH NETATMO | WNRL10WH
Get advanced control of your lights from any smart device, from anywhere. Optimized for whole home use. Requires Smart Gateway. Tru-UniversalDimmer and Plug-in versions also available.

SMART OUTLET WITH NETATMO | WNRR15WH
Get advanced control of power from any smart device, from anywhere. One outlet is app-controlled, the other is always on. Requires Smart Gateway. 15A and 20A versions available.

HOME/AWAY WIRELESS SMART SWITCH WITH NETATMO | WNRL33WH
Add to any wall or surface for one touch control of a full lighting scene. Requires Smart Gateway. Wake/Sleep version also available.

Dimmers

Conveniently conserve energy and create the perfect mood by adjusting dimmer light levels with a single slide.

NAME	PART NUMBER	DESCRIPTION	COLOR/FINISH	RATING	COMPATIBLE LOADS	COMPLIANCE
Incandescent Single-Pole/3-Way Dimmer	RH1103PTC RH1103PW	Usable in single-pole and 3-way applications. Features interchangeable faceplates.	Tri-Color* White	15A, 120V	1100W	, RoHS
Incandescent Single-Pole/3-Way Dimmer	RH703PDBCCV4 RH703PNICCV4 RH703PTC RH703PW	Usable in single-pole and 3-way applications. Features interchangeable faceplates.	Dark Bronze Nickel Tri-Color* White	120V	700W	, RoHS
0-10VLED/Fluorescent Dimmer	RH4FBL3PTC RH4FBL3PW	Features interchangeable faceplates.	Tri-Color* White	10A, 120V		, RoHS
Tru-Universal Single-Pole/3-Way Dimmer	RH703PTUTC RH703PTUW	The simplest solution to every dimming need, this dimmer self-calibrates to work with dimmable bulbs & loads (except 0-10V). Usable in single-pole and 3-way applications. Features interchangeable faceplates.	Tri-Color* White	120V, 60Hz	Incandescent, Halogen & ELV: 700W MLV: 500VA LED/CFL: 450W EFL: 5.5A	, RoHS
CFL/LED Dimmer (Not intended for electronic low voltage loads)	RHCL453PDBCCV4 RHCL453PGCCV4 RHCL453PNICCV4 RHCL453PTC RHCL453PW	Features interchangeable faceplates.	Dark Bronze Graphite Nickel Tri-Color* White	120 VAC, 60 Hz	450W CFL/LED; 700W Incandescent	, RoHS
Magnetic Low-Voltage Single-Pole/3-Way Dimmer	RHLV1103PTC RHLV1103PW	Usable in single-pole and 3-way applications. Features interchangeable faceplates.	Tri-Color* White	120 VAC	1100W	, RoHS

Note: Wall plates sold separately. Tri-color includes: White, Light Almond and Ivory. Bi-Color includes: Nickel & Dark Bronze
Due to manufacturer variations and modifications, we are unable to ensure indefinite dimming compatibility with any bulb or fixture.

NAME	PART NUMBER	DESCRIPTION	COLOR/FINISH	RATING	COMPATIBLE LOADS	COMPLIANCE
Magnetic Low-Voltage Single-Pole/3-Way Dimmer	RHLV703PTC RHLV703PW	Usable in single-pole and 3-way applications. Features interchangeable faceplates.	Tri-Color* White	120V	700W	, RoHS
2-Wire Fluorescent Dimmer	RHFB83PTC RHFB83PW	Features interchangeable faceplates.	Tri-Color* White	8A, 120V		, RoHS
Interchangeable Face Cover	RHKIT RHKITBK RHKITDB RHKITGRY RHKITI RHKITLA RHKITNI RHKITW RHKITGPCCV6	Features interchangeable faceplates.	Brown Black Dark Bronze Gray Ivory Light Almond Nickel White Graphite		Applies to all dimmers on pages 14& 15	, RoHS

Multi-Location Dimmers

Conveniently conserve energy and create the perfect mood by adjusting dimmer light levels with a single slide.

NAME	PART NUMBER	DESCRIPTION	COLOR/FINISH	RATING	COMPATIBLE LOADS	COMPLIANCE
Multi-Location Master Dimmer	HCL453PMMTC HCL453PMMW	Features interchangeable faceplates.	Tri-Color* White	120, 60Hz	700W Incandescent	, RoHS
Interchangeable Face Cover for Multi-Location Master Dimmer	HMKIT HMKITBK HMKITDB HMKITGRY HMKITI HMKITLA HMKITNI HMKITW	Features interchangeable faceplates.	Brown Black Dark Bronze Gray Ivory Light Almond Nickel White			, RoHS
Multi-Location Remote Dimmer	HMRTC HMRW	Features interchangeable faceplates.	Tri-Color* White	120, 60Hz		, RoHS
Interchangeable Face Cover for Multi-Location Remote Dimmer	HMRKIT HMRKITBK HMRKITDB HMRKITGRY HMRKITI HMRKITLA HMRKITNI HMRKITW	Features interchangeable faceplates.	Brown Black Dark Bronze Gray Ivory Light Almond Nickel White			, RoHS

Switches

Modern low-profilepaddle switches with no screws in sight.

NAME	PART NUMBER	DESCRIPTION	COLOR/FINISH	RATING	COMPLIANCE
15ASingle-Pole Switch* 	TM870 TM870BK TM870DBCC10 TM870GCC10 TM870GRY TM870I TM870ISL* TM870LA TM870LASL* TM870NICC10 TM870W TM870WSL*	15ASwitch. Part numbers with an asterisk indicate a model with included locator light.	Brown Black Dark Bronze Graphite Gray Ivory Ivory Light Almond Light Almond Nickel White White	15A, 120V	 , RoHS
3-WaySwitch* 	TM873 TM873BK TM873DBCC10 TM873GCC10 TM873GRY TM873I TM873ISL* TM873LA TM873LASL* TM873NICC10 TM873W TM873WSL*	15ASwitch. Part numbers with an asterisk indicate a model with included locator light.	Brown Black Dark Bronze Graphite Gray Ivory Ivory Light Almond Light Almond Nickel White White	15A, 120V	 , RoHS
15A4-Way Switch 	TM874 TM874BK TM874DBCC6 TM874GCC6 TM874I TM874ISL* TM874LA TM874LASL* TM874NICC6 TM874W TM874WSL*	15ASwitch. Part numbers with an asterisk indicate a model with included locator light.	Brown Black Dark Bronze Graphite Ivory Ivory Light Almond Light Almond Nickel White White	15A, 120V	 , RoHS

* These switches are identical

Fan Controls

NAME	PARTNUMBER	DESCRIPTION	COLOR/FINISH	RATING	COMPLIANCE
Fan Speed Control De-Hummer, Single-Pole/3-Way 	RHDH163PGCCV4 RHDH163PTC RHDH163PBCCCV4	Usable in single-pole and 3-way applications.	Graphite Tri-Color* Bi-Color *	1.6A, 120V	 , RoHS
Fan Speed Control De-Hummer, Single-Pole/3-Way 	RHDH163PW	Usable in single-pole and 3-way applications.	White	1.6A, 120V	 , RoHS

Note: Wall plates sold separately.

Combination Switches

Modern low-profilepaddle switches with no screws in sight.

NAME	PART NUMBER	DESCRIPTION	COLOR/FINISH	RATING	COMPLIANCE
Two Single-Pole Switches & Single-Pole/3-Way Switch 	RCD113 RCD113BK RCD113GRY RCD113I RCD113LA RCD113W	Usable in single-pole and 3-way applications. Features a locator light.	Brown Black Gray Ivory Light Almond White	15A, 120/125V	 , RoHS
Two Single-Pole Switches 	RCD11 RCD11BKCC6 RCD11GRY RCD11I RCD11LA RCD11W	Usable in single-pole applications. Features a locator light.	Brown Black Gray Ivory Light Almond White	15A, 120/125V	 , RoHS
Two Single-Pole/3-Way Switches* 	RCD33BK RCD33GRY RCD33I RCD33LA RCD33W	Usable in single-pole and 3-way applications. Features a locator light.	Black Gray Ivory Light Almond White	15A, 120/125V	 , RoHS
Single-Pole/3-Way Switch & Tamper-Resistant Single Outlet* 	RCD38TRBK RCD38GRY RCD38TRI RCD38TRLA RCD38TRW	Usable in single-pole and 3-way applications. Features a locator light.	Black Gray Ivory Light Almond White	15A, 120/125V	 , RoHS
Locator Light Module 	RCDLM		NA		 , RoHS

* These switches are identical

Note: Wall plates sold separately.

Sensors

NAME	PART NUMBER	DESCRIPTION	COLOR/FINISH	RATING	COMPLIANCE
120VSingle-Pole/3-Way Occupancy Sensor	RRW600FPG RRW600UTC RRW600UBCCCV4	Features interchangeable faceplates.	Graphite Tri-Color* Bi-Color*	120V	 LISTED , RoHS
120VSingle-Pole Vacancy Sensor	RRW600VTC	Features interchangeable faceplates.	Tri-Color*	120V	 LISTED , RoHS

Timers

NAME	PARTNUMBER	DESCRIPTION	COLOR/FINISH	RATING	COMPLIANCE
4-Button Digital Timer	RT2BK RT2DBCCV4 RT2I RT2LA RT2NICCV4 RT2W	Preset time delay options include 10,20, 30 or 60 min. Includes LED indicator light.	Black Dark Bronze Ivory Light Almond Nickel White	120V	 LISTED , RoHS

Note: Wall plates sold separately.
*Tri-colorincludes: White, Light Almond and Ivory.
*Bi-Color includes: Nickel & Dark Bronze

Outlets

NAME	PART NUMBER	DESCRIPTION	COLOR/FINISH RATING	SH	NEMA CONFIG. NUMBER	COMPLIANCE
Tamper-Resistant Outlet	885TR 885TRBK 885TRDBCC12 885TRGCC12 885TRGRY 885TRI 885TRLA 885TRNICC12 885TRW	Tamper-resistant outlet featuring patented invisí-shutters for discreet protection.	Brown Black Dark Bronze Graphite Gray Ivory Light Almond Nickel White	15A, 120/125V	5-15R	 LISTED , RoHS
	TR26352R TR26352RBK TR26352RDBCC6 TR26352RGCC6 TR26352RGRY TR26352RI TR26352RLA TR26352RNICC6 TR26352RW		Brown Black Dark Bronze Graphite Gray Ivory Light Almond Nickel White	20A, 125V	5-20R	 LISTED , RoHS
Weather-Resistant Outlet	885TRWR 885TRWRI 885TRWRLA 885TRWRW	NEC compliant for both tamper- and weather-resistance.	Brown Ivory Light Almond White	15A, 125V	5-15R	 LISTED , RoHS
radiant In-Wall Outlet Relocation Kit	IWPE-WH IWPEUSBAC-WH	Extends power from any hard-to-reach outlet to a more convenient location. Available versions include a Tamper-Resistant Out-let or a Tamper-ResistantUSB Type-A/C Outlet.	White	15A	5-15R	 LISTED , RoHS

GFCI

NAME	PART NUMBER	DESCRIPTION	COLOR/ FINISH	RATING	NEMA CONFIG. NUMBER	COMPLIANCE
 Tamper-Resistant Self-Test GFCI Outlet with Night Light	1597NLTTRBKCC4 1597NLTTRDBCC4 1597NLTTRI 1597NLTTRLA 1597NLTTRNICC4 1597NLTTRW	Provides superior, point-of-use ground-fault protection. Self-tests every three seconds to ensure it is ready to protect. Features built-in night light.	Black Dark Bronze Ivory Light Almond Nickel White	15A, 125V	5-15R	 , RoHS
	2097NLTTRGRY 2097NLTTRI 2097NLTTRLA 2097NLTTRW		Gray Ivory Light Almond White	20A, 125V	5-20R	 , RoHS
 Single-Pole Switch with Tamper-Resistant Self-Test GFCI Outlet	1597SWTTRBKCC4 1597SWTTRICC4 1597SWTTRLACC4 1597SWTTRWCC4	Combination switch and GFCI outlet. Provides superior, point-of-use ground-fault protection. Self-tests every three seconds to ensure it is ready to protect.	Black Ivory Light Almond White	15A, 125V	5-15R	 , RoHS
 Tamper-Resistant Self-Test GFCI Outlet	1597TR 1597TRBK 1597TRDBCC4 1597TRGCC4 1597TRGRY 1597TRI 1597TRLA 1597TRNICC4 1597TRW	Provides superior, point-of-use ground-fault protection. Self-tests every three seconds to ensure it is ready to protect.	Brown Black Dark Bronze Graphite Gray Ivory Light Almond Nickel White	15A, 125V	5-15R	 , RoHS
	2097TR 2097TRBK 2097TRGRY 2097TRI 2097TRLA 2097TRW 2097TRNI 2097TRDB 2097TRG		Brown Black Gray Ivory Light Almond White Nickel Dark Bronze Graphite	20A, 125V	5-20R	 , RoHS
 Tamper-Resistant Self-Test GFCI Outlet with Audible Alarm	1597TRA 1597TRABK 1597TRAI 1597TRALA 1597TRAW	Provides superior, point-of-use ground-fault protection. Self-tests every three seconds to ensure it is ready to protect. Features an audible alarm to alert users to trips or failures, perfect for sub-pumps and deep freezers.	Brown Black Ivory Light Almond White	15A, 125V	5-15R	 , RoHS
 Spec-Grade Weather-Resistant Self-Test GFCI Outlet	1597TRWR 1597TRWRBK 1597TRWRGRY 1597TRWRI 1597TRWRLA 1597TRWRW	Provides superior, point-of-use ground-fault protection for outdoor use. NEC compliant for weather-resistance. Self-tests every three seconds to ensure it is ready to protect.	Brown Black Gray Ivory Light Almond White	15A, 125V	5-15R	 , RoHS

Note: Wall plates sold separately.

Dual-FunctionAFCI/GFCI & AFCI

NAME	PART NUMBER	DESCRIPTION	COLOR/ FINISH	RATING	NEMA CONFIG. NUMBER	COMPLIANCE
 Tamper-Resistant Dual-Function AFCI/GFCI Outlet	AFGF152TR AFGF152TRBK AFGF152TRGRY AFGF152TRI AFGF152TRLA AFGF152TRW	Provides protection against arc-and ground-fault occurrences. Includes individual indicator lights for each fault type.	Brown Black Gray Ivory Light Almond White	15A, 125V	5-15R	 , RoHS
	AFGF202TR AFGF202TRBK AFGF202TRGRY AFGF202TRI AFGF202TRLA AFGF202TRW		Brown Black Gray Ivory Light Almond White	20A, 125V	5-20R	 , RoHS
 Tamper-Resistant Branch Circuit AFCI Outlet	AF152TR AF152TRBK AF152TRGRY AF152TRI AF152TRLA AF152TRW	Provides point-of-use arc-fault protection.	Brown Black Gray Ivory Light Almond White	15A, 125V	5-15R	 , RoHS
	AF202TR AF202TRBK AF202TRGRY AF202TRI AF202TRLA AF202TRW		Brown Black Gray Ivory Light Almond White	20A, 125V	5-20R	 , RoHS
 Dead Front Dual-Function AFCI/GFCI Outlet	AFGF202DFI AFGF202DFLA AFGF202DFW	Provides protection against arc-fault and ground-fault occurrences.	Ivory Light Almond White	20A, 125V		 , RoHS
 Dead Front Branch Circuit AFCI Outlet	AF202DFI AF202DFLA AF202DFW	Point-of-Use Arc Fault Detection	Ivory Light Almond White	20A, 125V		 , RoHS

Note: Wall plates sold separately.

USB Charging Solutions

NAME	PART NUMBER	DESCRIPTION	COLOR/FINISH	RATING	NEMA CONFIG NUMBER	COMPLIANCE
Wireless Charger 	RWC826USBWCCV2 RWC826USBICCV2 RWC826USBLACCV2 RWC826USBBKCCV2	Installs in place of a single-gang outlet to provide Qi wireless charging, as well as a tamper-resistant duplex outlet with USB Type-A port.	White Ivory Light Almond Black	15A, 125V	5-15R	 ^{US} LISTED, RoHS
15ATamper-Resistant USB Type-C/COutlet 	R26USBCCBK R26USBCCDBCCV4 R26USBCCG R26USBCCI R26USBCCLA R26USBCCNICCV6 R26USBCCW	Outlet with two built-in USB Type-C ports, for use with the newer USB Type-C and its conveniently reversible connector. Features discreet tamper-resistance through patented invis-shutters.	Black Dark Bronze Graphite Ivory Light Almond Nickel White	15A, 120V	3.1Amp	 ^{US} LISTED, RoHS
15ATamper-Resistant USB Type-A/COutlet 	R26USBACBK R26USBACDBCCV4 R26USBACG R26USBACI R26USBACLA R26USBACNICCV6 R26USBACW	Outlet features built-in ports for both USB Type-A and USB Type-C to fit any device, no adapter needed. Features discreet tamper-resistance through patented invis-shutters.	Black Dark Bronze Graphite Ivory Light Almond Nickel White	15A, 120V	3.1Amp	 ^{US} LISTED, RoHS
15ATamper-Resistant USB Type-A/AOutlet 	TM826USBBK TM826USBDDBCCV4 TM826USBGCCV4 TM826USBI TM826USBLA TM826USBNICCV6 TM826USBW	Outlet with two built-in USB Type-A ports. Features discreet tamper-resistance through patented invis-shutters.	Black Dark Bronze Graphite Ivory Light Almond Nickel White	15A, 120V	3.1Amp	 ^{US} LISTED, RoHS
Quad USB Charger 	TM8USB4BKCC6 TM8USB4ICCV6 TM8USB4LACCV6 TM8USB4NICCV6 TM8USB4WCCV6	Charge more devices simultaneously with four USB Type-A ports in a single device. Features 4.2A of total charging capacity.	Black Ivory Light Almond Nickel White	15A, 125V		 ^{US} LISTED, RoHS

Note: Wall plates sold separately.

Ultra-FastUSB Outlets

NAME	PART NUMBER	DESCRIPTION	COLOR/ FINISH	RATING	NEMA CONFIG NUMBER	COMPLIANCE
 15ATamper-Resistant Ultra-Fast USB Type-A/C Outlet	R26USBAC6BK R26USBAC6DBCCV4 R26USBAC6G R26USBAC6I R26USBAC6LA R26USBAC6NICCV4 R26USBAC6W	USB Outlet with industry-leading amperage to charge devices up to 40% faster. Includes ports for USB Type-A and Type-C to fit any device, no adapter needed.	Black Dark Bronze Graphite Ivory Light Almond Nickel White	6A	5-15R	 ^{US} LISTED, RoHS
 15ATamper-Resistant Ultra-Fast USB Type-C/C Outlet	R26USBCC6BK R26USBCC6DBCCV4 R26USBCC6G R26USBCC6I R26USBCC6LA R26USBCC6NICCV4 R26USBCC6W	USB Outlet with industry-leading amperage to charge devices up to 40% faster. Features two built-in USB Type-C ports for future-proof charging of the latest and upcoming devices.	Black Dark Bronze Graphite Ivory Light Almond Nickel White	6A	5-15R	 ^{US} LISTED, RoHS
 Outdoor Ultra-Fast USB Type-A/C Outlet	WRR26USBAC6BK WRR26USBAC6I WRR26USBAC6LA WRR26USBAC6W	Bring USB charging outdoors to decks, patios and porches. The outlet is UL listed to UL498 for weather resistance and must be installed in a weatherproof enclosure per NEC requirements.	Black Ivory Light Almond White	6A, 125V	5-15R	 ^{US} LISTED, RoHS

Ultra-FastPLUS Power Delivery

NAME	PART NUMBER	DESCRIPTION	COLOR/FINISH	RATING	NEMA CONFIG NUMBER	COMPLIANCE
 Tamper-Resistant Ultra-Fast PLUS Power Delivery USB Type-C/C Outlet	R26USBPDBK R26USBPD R26USBPDDDBCC6 R26USBPDGCC6 R26USBPDGRY R26USBPDI R26USBPDLA R26USBPDNICCV6 R26USBPDW TR20USBPDBK TR20USBPD TR20USBPDDDB TR20USBPDG TR20USBPDGRY TR20USBPDI TR20USBPDLA TR20USBPDNI TR20USBPDW	Charges devices up to 2X faster by combining our ultra-fast amperage with advanced Power Delivery. Includes two future-proof USB Type-C ports.	Black Brown Dark Bronze Graphite Gray Ivory Light Almond Nickel White Black Brown Dark Bronze Graphite Gray Ivory Light Almond Nickel White	6A, 15A, 125V,  6A, 20A, 125V, 	5-15R 5-15R	 ^{US} LISTED, RoHS

Note: Wall plates sold separately.

GFCI USB

NAME	PART NUMBER	DESCRIPTION	COLOR/ FINISH	RATING	NEMA CONFIG. NUMBER	COMPLIANCE
 Tamper-Resistant Self-Test GFCI USB Type-A/A Outlet	1597TRUSBAABK 1597TRUSBAA 1597TRUSBAADB 1597TRUSBAAG 1597TRUSBAAGRY 1597TRUSBAAI 1597TRUSBAALA 1597TRUSBAANI 1597TRUSBAAW	The first-ever GFCI Outlet with built-in USB charging, offering superior ground-fault protection and modern convenience in a single solution. Includes two USB Type-A ports.	Black Brown Dark Bronze Graphite Gray Ivory Light Almond Nickel White	15A, 125V	5-15R	 , RoHS
	2097TRUSBAABK 2097TRUSBAA 2097TRUSBAADB 2097TRUSBAAG 2097TRUSBAAGRY 2097TRUSBAAI 2097TRUSBAALA 2097TRUSBAANI 2097TRUSBAAW		Black Brown Dark Bronze Graphite Gray Ivory Light Almond Nickel White	20A, 125V	5-20R	 , RoHS
 Tamper-Resistant Self-Test GFCI USB Type-A/C Outlet	1597TRUSBACBK 1597TRUSBAC 1597TRUSBACDB 1597TRUSBACG 1597TRUSBACGRY 1597TRUSBACI 1597TRUSBACLA 1597TRUSBACNI 1597TRUSBACW	The first-ever GFCI Outlet with built-in USB charging, offering superior ground-fault protection and modern convenience in a single solution. Includes USB Type-A and USB Type-C ports to charge any and all your devices, no adapter necessary.	Black Brown Dark Bronze Graphite Gray Ivory Light Almond Nickel White	15A, 125V	5-15R	 , RoHS
	2097TRUSBACBK 2097TRUSBAC 2097TRUSBACDB 2097TRUSBACG 2097TRUSBACGRY 2097TRUSBACI 2097TRUSBACLA 2097TRUSBACNI 2097TRUSBACW		Black Brown Dark Bronze Graphite Gray Ivory Light Almond Nickel White	20A, 125V	5-20R	 , RoHS
 Outdoor Self-Test GFCI USB Type-A/C Outlet	1597TRWRUSBACBK 1597TRWRUSBACGRY 1597TRWRUSBACI 1597TRWRUSBACLA 1597TRWRUSBACW	Engineered for outdoor use, this version of our first-of-its-kind GFCI USB Outlet also features weather-resistance to bring superior ground-fault protection and modern convenience to patios, pool areas and more – all in a single solution. Includes USB Type-A and USB Type-C ports to charge any and all your devices, no adapter necessary.	Black Gray Ivory Light Almond White	15A, 125V	5-15R	 , RoHS
	2097TRWRUSBACBK 2097TRWRUSBACGRY 2097TRWRUSBACI 2097TRWRUSBACLA 2097TRWRUSBACW		Black Gray Ivory Light Almond White	20A, 125V	5-20R	 , RoHS
 Tamper-Resistant Self-Test GFCI USB Type-C/C Outlet	1597TRUSBCCBK 1597TRUSBCC 1597TRUSBCCDB 1597TRUSBCCG 1597TRUSBCCGRY 1597TRUSBCCI 1597TRUSBCCLA 1597TRUSBCCNI 1597TRUSBCCW	The first-ever GFCI Outlet with built-in USB charging, offering superior ground-fault protection and modern convenience in a single solution. Includes two future-proof USB Type-C ports to accommodate the latest and upcoming devices.	Black Brown Dark Bronze Graphite Gray Ivory Light Almond Nickel White	15A, 125V	5-15R	 , RoHS
	2097TRUSBCCBK 2097TRUSBCC 2097TRUSBCCDB 2097TRUSBCCG 2097TRUSBCCGRY 2097TRUSBCCI 2097TRUSBCCLA 2097TRUSBCCNI 2097TRUSBCCW		Black Brown Dark Bronze Graphite Gray Ivory Light Almond Nickel White	20A, 125V	5-20R	 , RoHS

NAME	PART NUMBER	DESCRIPTION	COLOR/ FINISH	RATING	NEMA CONFIG. NUMBER	COMPLIANCE
 Outdoor Self-Test GFCI USB Type-C/C Outlet	1597TRWRUSBCCBK 1597TRWRUSBCCGRY 1597TRWRUSBCCI 1597TRWRUSBCCLA 1597TRWRUSBCCW	Engineered for outdoor use, this version of our first-of-its-kind GFCI USB Outlet also features weather-resistance to bring superior ground-fault protection and modern convenience to patios, pool areas and more – all in a single solution. Includes two future-proof USB Type-C ports to accommodate the latest and upcoming devices.	Black Gray Ivory Light Almond White	15A, 125V	5-15R	 , RoHS
	2097TRWRUSBCCBK 2097TRWRUSBCCGRY 2097TRWRUSBCCI 2097TRWRUSBCCLA 2097TRWRUSBCCW		Black Gray Ivory Light Almond White	20A, 125V	5-20R	 , RoHS

Night Lights

NAME	PART NUMBER	DESCRIPTION	COLOR/ FINISH	RATING	NEMA CONFIG. NUMBER	COMPLIANCE
 Night Light with Two 15A Tamper-Resistant Outlets	NTL885TRBKCC6 NTL885TRICC6 NTL885TRLACC6 NTL885TRNICC6 NTL885TRW	Five Adjustable Light Settings	Black Ivory Light Almond Nickel White	15A, 120/125V	5-15R	 , RoHS
	NTL873BKCC6 NTL873ICC6 NTL873LACC6 NTL873NICC6 NTL873WCC6		Black Ivory Light Almond Nickel White	15A, 120/125V		 , RoHS
 Night Light With Single-Pole, 3-Way Switch	NTL873BKCC6 NTL873ICC6 NTL873LACC6 NTL873NICC6 NTL873WCC6	Five Adjustable Light Settings	Black Ivory Light Almond Nickel White	15A, 120/125V		 , RoHS
 Full Night Light with Adjustable Light Levels	NTLFULLTC NTLFULLW	Five Adjustable Light Settings An optional louver is included for added light-level control	Tri-Color* White	120/125V		 , RoHS
	NTLFULLTC NTLFULLW					
 Horizontal Step Light	NTLHORZTCCC6 NTLHORZWCC6	Five Adjustable Light Settings	Tri-Color* White	120/125V		 , RoHS
	NTLHORZTCCC6 NTLHORZWCC6					

Note: Wall plates sold separately.

radiant with Netatmo

Control lights and power, from anywhere, with the ultra-reliable smart lighting solution optimized for whole-home use. Works with Amazon Alexa, Google Home and Apple HomeKit. Compatible with adorne with Netatmo.

NAME	PARTNUMBER	DESCRIPTION	COLOR/FINISH	RATING	COMPATIBLE LOADS	COMPLIANCE
Smart Gateway with Netatmo 	WNRH1WH WNRH1LA WNRH1NI	Creates a robust and dedicated network as the foundation of the Netatmo smart lighting solution.	White Light Almond Nickel			 , RoHS
Smart Surface-Mount Gateway with Netatmo 	WNRH2WH WNRH2LA WNRH2NI	Creates a robust and dedicated network as the foundation of the Netatmo smart lighting solution. Installs beside an outlet or switch.	White Light Almond Nickel			 , RoHS
Smart Switch with Netatmo 	WNRL10WH WNRL10LA WNRL10NI	Control lights from anywhere. Gateway required.	White Light Almond Nickel	15A, 120V		 , RoHS
Smart Tru-Universal Dimmer with Netatmo 	WNRL50WH WNRL50LA WNRL50NI	The simplest solution to every dimming need, this dimmer self-calibrates to work with dimmable bulbs & loads (except 0-10V).	White Light Almond Nickel	15A, 120V	Incandescent, Halogen & ELV: 700W, MLV: 500VA, LED/ CFL: 450W (not compatible with 0-10VLED drivers), EFL: 5.5A	 , RoHS
Wireless Smart Switch with Netatmo 	WNRL23WH WNRL23LA WNRL23NI	Can be added to any wall or surface for easy 3-way control, no wiring required. Must be paired with a Smart Switch with Netatmo. Battery-operated.	White Light Almond Nickel			 , RoHS
Wireless Smart Dimmer with Netatmo 	WNRL63WH WNRL63LA WNRL63NI	Can be added to any wall or surface for easy 3-way dimming control, no wiring required. Must be paired with a Smart Tru-Universal Dimmer with Netatmo. Battery-operated.	White Light Almond Nickel			 , RoHS

Note: Wall plates included with all radiant with Netatmo products.

NAME	PART NUMBER	DESCRIPTION	COLOR/FINISH	RATING	NEMA/COMPATIBLE LOADS	COMPLIANCE
Home/Away Wireless Smart Switch with Netatmo 	WNRL33WH WNRL33LA WNRL33NI	Controls a scene of multiple lights, turning the lights on (or off), simultaneously, with just a single touch. Add to any wall or surface, no wiring required. Battery-operated.	White Light Almond Nickel			 , RoHS
Wake/Sleep Wireless Smart Switch with Netatmo 	WNRL43WH WNRL43LA WNRL43NI	Controls a scene of multiple lights, turning the lights on (or off), simultaneously, with just a single touch. Add to any wall or surface, no wiring required. Battery-operated.	White Light Almond Nickel			 , RoHS
Smart Outlet with Netatmo 	WNRR15WH WNRR15LA WNRR15NI WNRR20WH WNRR20LA WNRR20NI	Control power from anywhere. One outlet is app-controlled, the other is always on. Gateway required.	White Light Almond Nickel White Light Almond Nickel	15A, 125V, TR 20A, 125V, TR	5-15R 5-20R	 , RoHS
Smart Plug-In Switch with Netatmo 	WNP10	Plug-in to an existing outlet for smart control of lamps and small appliances, no installation required.	White			 , RoHS
Smart Plug-In Tru-Universal Dimmer with Netatmo 	WNP20	Plug into an existing outlet to gain smart dimming control. The simplest solution to every dimming need, this dimmer self-calibrates to work with dimmable bulbs & loads (except 0-10V).	White		Incandescent, Halogen & ELV: 700W, MLV: 500VA, LED/ CFL: 450W (not compatible with 0-10VLED drivers), EFL: 5.5A	 , RoHS
Smart Switch Starter Kit with Netatmo 	WNRH10KITWH WNRH10KITLA WNRH10KITNI	Kit includes (1) Smart Switch with Netatmo, (1) Smart Surface-Mount Gateway with Netatmo, (1) Home/Away Wireless Smart Switch with Netatmo	White Light Almond Nickel	15A, 120V		 , RoHS
Smart Outlet Starter Kit with Netatmo 	WNRH15KITWH WNRH15KITLA WNRH15KITNI	Kit includes (1) 15ASmart Outlet with Netatmo, (1) Smart Surface-Mount Gateway with Netatmo, (1) Home/Away Wireless Smart Switch with Netatmo	White Light Almond Nickel	15A, 125V, TR		 , RoHS

Note: Wall plates included with all radiant with Netatmo products.

Screwless Wall Plates

How to build a better wall plate? Try clean lines and a low profile with no screws in sight.

NAME	GANGS	PARTNUMBER	NAME	GANGS	PARTNUMBER
Black	1-Gang 2-Gang 3-Gang 4-Gang 5-Gang 6-Gang	RWP26BK RWP262BK RWP263BK RWP264BK RWP265BK RWP266BK	Ivory	1-Gang 2-Gang 3-Gang 4-Gang 5-Gang 6-Gang	RWP26I RWP262I RWP263I RWP264I RWP265I RWP266I
Brown	1-Gang 2-Gang 3-Gang 4-Gang 5-Gang 6-Gang	RWP26 RWP262 RWP263 RWP264 RWP265 RWP266	Light Almond	1-Gang 2-Gang 3-Gang 4-Gang 5-Gang 6-Gang	RWP26LA RWP262LA RWP263LA RWP264LA RWP265LA RWP266LA
Gray	1-Gang 2-Gang 3-Gang 4-Gang 5-Gang 6-Gang	RWP26GRY RWP262GRY RWP263GRY RWP264GRY RWP265GRY RWP266GRY	White	1-Gang 2-Gang 3-Gang 4-Gang 5-Gang 6-Gang	RWP26W RWP262W RWP263W RWP264W RWP265W RWP266W

Metallic Screwless Wall Plates

NAME	GANGS	PARTNUMBER	NAME	GANGS	PARTNUMBER
Dark Bronze	1-Gang 2-Gang 3-Gang 4-Gang 5-Gang 6-Gang	RWP26DBCC6 RWP262DBCC6 RWP263DBCC6 RWP264DB RWP265DB RWP266DB	Nickel	1-Gang 2-Gang 3-Gang 4-Gang 5-Gang 6-Gang	RWP26NICC6 RWP262NICC6 RWP263NICC6 RWP264NI RWP265NI RWP266NI
Graphite	1-Gang 2-Gang 3-Gang 4-Gang 5-Gang 6-Gang	RWP26GCC6 RWP262GCC6 RWP263GCC6 RWP264CC6 RWP265G RWP266G			

