

LINKEO



ENCLOSURES TO FIT YOUR SCS
INSTALLATIONS AND BUDGET

EDITION
2018



GLOBAL SPECIALIST IN ELECTRICAL AND DIGITAL
BUILDING INFRASTRUCTURES



19" Freestanding cabinets


LINKEO




A complete solution for commercial sector requirements

The LINKEO 19" enclosures have been designed to be easy to install and totally functional. With the wide range of accessories that can be used with LINKEO enclosures, you have the benefit of a complete offer to meet the requirements of all your projects.







1 19" uprights with U marking and adjustable in depth



2 Pre-cut top and bottom cable entries
Cut-out on the roof for fan kits



3 Full glass door (reversible) with screen printing for perfect aesthetics



4 Removable side and rear panels with automatic grounding



5 Vertical cable guide (side and rear mount) and PDU support as option



- Equipped with levelling feet
- Can be linked using baying kit
- 2 delivery options :
mounted or flatpack

Linkeo 19" freestanding cabinets

cabinets and equipment



6 467 64



6 464 03



6 464 30



Technical characteristics p. 10

Pack	Cat.Nos	Linkeo 19" cabinets
		IP 20 – IK 08 baying cabinets Reversible front glass door with screen printing Removable side and rear panels Panels with automatic equipotential connection 4 sides locked with key lock Equipped with 2 x 19" uprights with U marking and adjustable in depth Pre-cut cable entries (top and bottom) To be fitted with brush cable entry Cat.No 6 464 28 Cut-out at the top for fan kit Equipped with levelling feet Loading capacity: 400 kg Anthracite grey RAL 7016
		Single front glass door
	Ready-assembled Flatpack	Capacity Height (mm) Width (mm) Depth (mm)
1	6 467 50 6 467 75	24 U 1226 600 600
1	6 467 51 6 467 76	24 U 1226 800 800
1	6 467 55 6 467 80	33 U 1626 600 600
1	6 467 56 6 467 81	33 U 1626 800 800
1	6 467 60 6 467 85	42 U 2026 600 600
1	6 467 61 6 467 86	42 U 2026 600 800
1	6 467 62 6 467 87	42 U 2026 600 1000
1	6 467 63 6 467 88	42 U 2026 800 600
1	6 467 64 6 467 89	42 U 2026 800 800
1	6 467 65 6 467 90	42 U 2026 800 1000
1	6 467 73 6 467 98	47 U 2248 800 800
1	6 467 74 6 467 99	47 U 2248 800 1000
		Extension cabinets with single glass door
		No side panels Supplied with baying kit
		Capacity Height (mm) Width (mm) Depth (mm)
1	6 467 70 6 467 95	42 U 2026 800 800
		Double front glass door
		Capacity Height (mm) Width (mm) Depth (mm)
1	6 467 66	42 U 2026 800 600
1	6 467 67	42 U 2026 800 800
1	6 467 68	42 U 2026 800 1000
		Linkeo baying kits
1	6 463 37	For joining 2 Linkeo 19" cabinets
		Linkeo 19" uprights
		Set of 2 additional 19" uprights
1	6 463 40	24 U
1	6 463 41	33 U
1	6 463 42	42 U
1	6 463 43	47 U

Pack	Cat.Nos	Linkeo plinths
		Metal plinths consisting of 4 corner blocks and 4 removable traps Height 100 mm Anthracite grey RAL 7016 For cabinets width x depth (mm):
1	6 464 00	600 x 600
1	6 464 01	600 x 800 or 800 x 600
1	6 464 02	600 x 1000
1	6 464 03	800 x 800
1	6 464 04	800 x 1000
		Casters
1	0 464 82	Set of 4 pivoting casters, 2 of which have brakes Total loading capacity on the 4 casters: 500 kg
		Linkeo fan kits
		Integrated thermostat, adjustable from - 10 to 80°C 2.5 m cord with 2P+E plug, 230 V~ Anthracite grey RAL 7016
1	6 464 30	2 fans
1	6 464 31	4 fans
		Linkeo cable management
		Brush cable entry
		To fit on top or bottom cabinet pre-cut cable entry Set of brush
1	6 464 28	
		Vertical cable guides
		Side or rear mounting on structure for cable bundles
1	6 464 20	For 33 U cabinet
1	6 464 21	For 42 U cabinet
1	6 464 22	For 47 U cabinet
		Cable management rings
		For cabinet width 800 mm. Fixes onto 19" uprights Usable dim.: 65 x 145 mm. Black RAL 9005
1	6 464 25	Set of 6 metal rings
		Vertical cable managers
		Set of 2 vertical panels to manage cords at the front side and on the whole height of the cabinet Mounted on the side of 19" uprights Supplied with brush feedthroughs and fingers for cords management every single U
1	6 464 26	For 42 U 800 mm wide cabinets
1	6 464 27	For 47 U 800 mm wide cabinets
		PDU support
		Vertical support for fixing to the rear side of the cabinet. For mounting vertically 19" and Zero-U PDU
1	6 464 15	For 42 U cabinets
1	6 464 16	For 47 U cabinets



Linkeo 19" freestanding cabinets

cabinets and equipment (continued)



Linkeo fixed shelves

Pack	Cat.Nos	
1	6 465 01	Black RAL 9005
1	6 465 02	Screw fixing on 2 x 19" uprights
		Height 2 U. Max. load: 15 kg
		Shelf depth 200 mm
		Shelf depth 360 mm
1	6 465 05	Screw fixing on 4 x 19" uprights
		Height 1 U
		Max. load: 50 kg
		Shelf depth 425
		For depth 600 mm
1	6 465 06	Shelf depth 625
		For depth 800 mm
1	6 465 07	Shelf depth 825
		For depth 1000 mm

Linkeo telescopic shelves

1	6 465 08	Screw fixing on 4 x 19" uprights. Height 1 U
		Max. load: 30 kg. Black RAL 9005
		Shelf depth 425
1	6 465 09	For depth 600 mm
		Shelf depth 625
1	6 465 10	For depth 800 mm
		Shelf depth 825
		For depth 1000 mm

19" management panels

1	6 465 20	Fitted with cable guide rings
1	6 465 21	1 U
		2 U

Linkeo 19" freestanding cabinets

Flatpack solution

Easy to carry
Easy to store
Easy to handle
Easy to mount:
- 16 minutes / 1 person
- dedicated installation sheet

High protection packaging (stackable)

Nota:

- cabinets delivered flatpack are exactly the same as the mounted ones. The only difference is the packaging.



Customization

1 Choose the size

Capacity	24 U	33 U	42 U	47 U
Width	600 or 800 mm			
Depth	600, 800 or 1000 mm			

2 Choose the color

Anthracite grey (RAL 7016) or light grey (RAL 7035)

3 Choose the openings



Doors

- screen-printed glass
- microperforated metal
- solid metal
in single or double version

4 Choose the equipments to mount at the factory

- cable managers
- fans
- plinths/casters
- shelves
- copper and fiber patch panels

LINKEO 19"

Wall-mounting cabinets

A full range !
Choose your level of
accessibility inside
the cabinet





► Fix side panels



19" version

10" version for small business applications


► Removable side panels



19" version

Pivoting 19" version

► Common features



- Reversible flat safety glass door with screen-printing and integrated lock



- Supplied with 2 x 19" uprights, adjustable in depth and with U marking
- Additional 19" uprights as option



- Rear, top and bottom pre-cut cable entries to be equipped with brush (provided with the cabinet)
- top perforations for natural ventilation (can be equipped with fan kit)

Linkeo 19" and 10" wall-mounting cabinets



IP 20 - IK 08
Equipped with :
- 1 reversible door made of screen-printed safety glass and with integrated lock
- 2 x 19" uprights with U marking and adjustable in depth
- 3 pre-cut cable entries (top, bottom and rear)
- 1 brush for a cable entry
- top perforations for natural ventilation
- panels with automatic grounding (ready assembled version)
- supplied with earthing kit (flatpack version)
Anthracite grey RAL 7016

Pack	Cat.Nos		Linkeo fix 19" cabinets			
			Fix side panels Delivered ready-assembled			
	Depth 450 mm	Depth 600 mm	Capacity	Height (mm)	Width (mm)	Loading capacity (kg)
1	6 462 00	6 462 10	6 U	358	600	18
1	6 462 01	6 462 11	9 U	492	600	27
1	6 462 02	6 462 12	12 U	625	600	36
1	6 462 03	6 462 13	15 U	758	600	45
1	6 462 04	6 462 14	18 U	892	600	54
1	6 462 05	6 462 15	21 U	1035	600	63
			Removable side panels For easy access at the side of the cabinet Opening with a lock (same key as the door) Delivered flatpack			
	Depth 450 mm	Depth 600 mm	Capacity	Height (mm)	Width (mm)	Loading capacity (kg)
1	6 462 50	6 462 60	6 U	358	600	18
1	6 462 51	6 462 61	9 U	471	600	27
1	6 462 52	6 462 62	12 U	604	600	36
1	6 462 53	6 462 63	15 U	738	600	45
1	6 462 54	6 462 64	18 U	871	600	54
1	6 462 55	6 462 65	21 U	1004	600	63

Linkeo pivoting 19" cabinets						
Cabinet composed of : - base (wall fixing), can accept 19" PDU - pivoting body allowing free access to the rear of the cabinet to facilitate installation and maintenance. Reversible pivoting direction. Delivered ready-assembled						
	Depth 610 mm		Capacity	Height (mm)	Width (mm)	Loading capacity (kg)
1	6 462 21		9 U	471	600	27
1	6 462 22		12 U	604	600	36
1	6 462 23		15 U	738	600	45
1	6 462 24		18 U	871	600	54
1	6 462 25		21 U	1004	600	63



Equipments for 19" cabinets

Linkeo 19" uprights		
Set of 2 additional 19" uprights To install at the rear of the cabinet		
1	6 462 42	12 U
1	6 462 43	15 U
1	6 462 44	18 U
1	6 462 45	21 U
1	6 462 48	Casters Set of 4 caster wheels for assembly on cabinets
1	6 462 38	Linkeo fan kit Kit contains: - 2 fans - 1 thermostat - ON/OFF switch Supplied with 2.3 m cable Power supply 230 V~ - 50/60 Hz


Pack	Cat.Nos	Equipments for 19" cabinets (continued)				
		Linkeo fixed shelves				
		Screw fixing on 2 x 19" uprights				
		Height 2 U				
		Max. load: 15 kg				
		Black RAL 9005				
1	6 465 01	Shelf depth 200 mm				
		For cabinets depth 400, 450 and 600 mm				
1	6 465 02	Shelf depth 360 mm				
		For cabinets depth 450 and 600 mm				
		19" management panels				
1	6 465 20	1 U				
1	6 465 21	2 U				
		Linkeo 10" cabinet				
		Compact cabinet suitable for small business applications				
		Delivered ready-assembled				
		Depth 300 mm	Capacity	Height (mm)	Width (mm)	Loading capacity (kg)
1	6 462 30		6 U	358	370	18

Equipments for 10" cabinets						
1	0 335 92	Modular empty panel 10" panel - 1 U For up to 2 LCS ² bloc units (copper or fiber) Supplied with screws and cage nuts				
1	0 462 23	Fixed shelf 1 U Depth 120 mm Max. load. 10 kg Black RAL 9005 Supplied with screws and cage nuts				
		10" Power Distribution Units (PDU) 230 V - 50/60 Hz power supply 1 U aluminium profile End cap with metallic brackets and cable holder shape Quick fixing (no screws) on 19" uprights With shutters and inclined at 55°				
1	6 468 01	4 x 2P+E outlets Black German standard 1 m power supply cord with 16 A 2P+E French/ German plug				
1	6 468 00	4 x 2P+E outlets Black French standard 1 m power supply cord with 16 A 2P+E French/German plug				
1	6 468 98	To be equipped with Mosaic wiring device modules Capacity: 8 Mosaic modules				

19" BATI-RACK



► Full access to the wiring



► Takes cable management sleeves for a perfect finish

19" Bati-rack



Technical characteristics p. 15

Pack	Cat.Nos	19" Bati-rack
		For housing 19" equipment in an air conditioned, secure, dust-free environment Comprises 2 or 4 x 19" uprights With levelling feet The 4-upright bati-rack takes shelves for enclosures depth 800 mm Supplied ready for assembly RAL 7035
1	0 463 95	Capacity
1	0 463 96	Height ⁽¹⁾ (mm)
		Width (mm)
		Depth (mm)
		Loading capacity (kg)
		Number of uprights
		2
		4
		Cable management sleeve
		Closed vertical feedthrough Reversible door For fixing on the right or left on the 19" uprights RAL 7035 Sleeve
1	0 463 97	
		Roof
1	0 464 98	Roof for 4-upright bati-rack 535 x 600 mm
		Set of 4 casters
1	0 464 99	For bati-rack Loading capacity on the 4 casters: 340 kg
		Shelves
		Black RAL 9005
		Screw fixing on 2 x 19" uprights
		Height 2 U
		Max. load: 15 kg
1	6 465 01	Shelf depth 200 mm
1	6 465 02	Shelf depth 360 mm
		Screw fixing on 4 x 19" uprights
		Height 1 U
1	6 465 06	Fixed shelf depth 625 mm. Max load: 50 kg
1	6 465 09	Telescopic shelf depth 625 mm. Max load: 30 kg
		19" management panels
		Fitted with cable guide rings
1	6 465 20	1 U
1	6 465 21	2 U



1: Without adjustment levelling feet (+ 27 to 42 mm with feet)

Linkeo 19" freestanding cabinets

General characteristics

Metallic extendable freestanding cabinets
RAL 7016 textured polyester coating providing excellent resistance to corrosion and scratching
Reversible single or double front glass door with screen-printing
Protection index (weatherproof) against solid objects and liquids: IP 20
Protection index against mechanical impacts: IK 08
Perforations in 19" uprights: 9.5 x 9.5 mm
Permissible load: 400 kg

Compliance with standards


Linkeo cabinets comply with the following standards:

IEC 60529 EN 60529	(NF C 20-010) Degrees of protection provided by enclosures (IP code)
IEC 62262 EN 62262	(NF EN 50102, NF C 20-015) Degrees of protection provided by enclosures for electrical equipment against external mechanical impacts (IK code)
IEC 60950-1 EN 60950-1 C 77-210-1	Safety of data processing equipment
EIA-310-E	Cabinets, racks, panels and associated equipment (ANSI/EIA-310-E-2005)
IEC 60297-3-100 DIN 41414-7	(NF C 20-150, NF C 20-151) Dimensions of mechanical structures of the 482.6 mm (19 in) series

Linkeo cabinets can be integrated in installations complying with the following standards:

EN 50173-1	Information technology - Generic cabling systems
EN 50174-1 & 2 C 90-480-1 & 2	Information technology - Cabling installation
ISO IEC 11801	Information technology - Generic cabling for customer premises
NF C 15-100 Part 4-41	Low voltage electrical installations - recommendations
IEC 60364-4-41	Low voltage electrical installations - Protection for safety - Protection against electric shock

Dimensions (mm)



Cabinets with single front door

Cabinet dimensions	Overall dimensions				
	H ⁽¹⁾	W	D	A	B
24 U 600 x 600	1226	610	630	1138	1210
24 U 800 x 800		810	830	1525	1610
33 U 600 x 600	1626	610	630	1138	1210
33 U 800 x 800		810	830	1525	1610
42 U 600 x 600	2026	610	630	1138	1210
42 U 600 x 800		610	830	1138	1410
42 U 600 x 1000		610	1030	1138	1610
42 U 800 x 600		810	630	1525	1410
42 U 800 x 800		810	830	1525	1610
42 U 800 x 1000		810	1030	1525	1810
47 U 800 x 800	2248	810	830	1525	1610
47 U 800 x 1000		810	1030	1525	1810

1: Without adjustment levelling feet (+19 to 39 mm with feet)



Cabinets with double front door

Cabinet dimensions	H ⁽¹⁾	W	D	A	B
42 U 800 x 600	2026	810	630	1164	1011
42 U 800 x 800			830		1211
42 U 800 x 1000			1030		1411

1: Without adjustment levelling feet (+19 to 39 mm with feet)

Linkeo 19" freestanding cabinets (continued)


Usable dimensions (mm)



Cabinet dimensions	A ⁽¹⁾	Usable area			E	Glass window Door
		B	C	D		
24 U 600 x 600	630	1081	490	490	425	1073 x 360
24 U 800 x 800	830		690	690	625	1073 x 450
33 U 600 x 600	630	1481	490	490	425	1473 x 360
33 U 800 x 800	830		690	690	625	1473 x 450
42 U 600 x 600	630	1881	490	490	425	1873 x 360
42 U 600 x 800	830			690	625	
42 U 600 x 1000	1030		690	490	425	1873 x 450
42 U 800 x 600	630			690	625	
42 U 800 x 800	830	2103	690	690	625	2095 x 450
42 U 800 x 1000	1030			890	825	
47 U 800 x 800	830	2103	690	690	625	2095 x 450
47 U 800 x 1000	1030			890	825	


1: Overall dimensions
2: Can be adjusted in 25 mm steps

Plinths for Linkeo cabinets (mm)




Cabinet dimensions Width x Depth	Overall		Fixing		Usable area	
	A	B	C	D	E	F
600 x 600	599	599	478	478	449	449
600 x 800	599	799	478	678	449	649
600 x 1000	799	599	678	478	649	449
800 x 600	799	799	678	678	649	649
800 x 800	599	999	478	878	449	849
800 x 1000	799	999	678	878	649	849

Linkeo fan kits (mm)



Linkeo 19" freestanding cabinets (continued)

Linkeo shelves (mm)




Cat.Nos	D	Usable width		
		W1	W2	W3
6 465 01	200	435		
6 465 02	360	435		
6 465 05	425		440	
6 465 06	625		440	
6 465 07	825		440	
6 465 08	425			410
6 465 09	625			410
6 465 10	825			410


Linkeo vertical cable guides

33 U guide: 1486 x 300 x 25 mm
 42 U guide: 1886 x 300 x 25 mm
 47 U guide: 2105 x 300 x 25 mm

Side mounting




Vertical cable managers 6 464 26/27




PDU supports 6 464 15/16 (mm)

Front view



Side view



Linkeo 19" wall-mounting cabinets

General characteristics

Metal wall-mounting cabinets
RAL 7016 textured polyester coating providing excellent resistance to corrosion and scratching
Safety glass door
Protection index (weatherproof) against solid objects and liquids: IP 20
Protection index against mechanical shocks: IK 08
Perforations in 19" uprights: 9.5 x 9.5 mm
Permissible load: 3 kg/U

Compliance with standards


Linkeo cabinets comply with the following standards:

IEC 60529 EN 60529	(NF C 20-010) Degrees of protection provided by enclosures (IP code)
IEC 62262 EN 62262	(EN 50102, NF C 20-015) Degrees of protection provided by enclosures for electrical equipment against external mechanical impacts (IK code)
IEC 60950-1 EN 60950-1 C 77-210-1	Safety of data processing equipment
EIA-310-E	Cabinets, racks, panels and associated equipment (ANSI/EIA-310-D-2005)
IEC 60297-3-100 DIN 41414-7	(NF C 20-150, NF C 20-151) Dimensions of mechanical structures of the 482.6 mm (19 in) series

Linkeo cabinets can be integrated in installations complying with the following standards:

EN 50173-1	Information technology - Generic cabling systems
EN 50174-1 & 2 C 90-480-1 & 2	Information technology - Cabling installation
ISO IEC 11801	Information technology - Generic cabling for customer premises
NF C 15-100 Part 4-41	Low voltage electrical installations - Recommendations
UTE C90-483	Residential cabling for communication networks
IEC 60364-4-41	Low voltage electrical installations - Protection for safety - Protection against electric shock


Dimensions (mm)




		Cat.Nos	Capacity	Height	Width	Depth
19" fix cabinet	fix side panels	6 462 00	6 U	358	600	450
		6 462 01	9 U	492	600	450
		6 462 02	12 U	625	600	450
		6 462 03	15 U	758	600	450
		6 462 04	18 U	892	600	450
		6 462 05	21 U	1035	600	450
		6 462 10	6 U	358	600	600
		6 462 11	9 U	492	600	600
		6 462 12	12 U	625	600	600
		6 462 13	15 U	758	600	600
		6 462 14	18 U	892	600	600
		6 462 15	21 U	1035	600	600
	removable side panels	6 462 50	6 U	338	600	450
		6 462 51	9 U	471	600	450
		6 462 52	12 U	604	600	450
		6 462 53	15 U	738	600	450
		6 462 54	18 U	871	600	450
		6 462 55	21 U	1004	600	450
		6 462 60	6 U	338	600	600
		6 462 61	9 U	471	600	600
		6 462 62	12 U	604	600	600
		6 462 63	15 U	738	600	600
		6 462 64	18 U	871	600	600
		6 462 65	21 U	1004	600	600
19" pivoting cabinets		6 462 21	9 U	471	600	610
		6 462 22	12 U	604	600	610
		6 462 23	15 U	738	600	610
		6 462 24	18 U	871	600	610
		6 462 25	21 U	1004	600	610
10" fix cabinet		6 462 30	6 U	358	370	300

Door opening (mm)


19" fix cabinets with fix side panels Cat.Nos 6 462 00/.../15




19" fix cabinets with removable side panels Cat.Nos 6 462 50/.../65



19" pivoting cabinets Cat.Nos 6 462 21/.../25




10" cabinet Cat.No 6 462 30




		Cat.Nos	Capacity	A	B
19" fix cabinet	fix side panels	6 462 00	6 U	930	795
		6 462 01	9 U	930	795
		6 462 02	12 U	930	795
		6 462 03	15 U	930	795
		6 462 04	18 U	930	795
		6 462 05	21 U	930	795
		6 462 10	6 U	1130	795
		6 462 11	9 U	1130	795
		6 462 12	12 U	1130	795
		6 462 13	15 U	1130	795
		6 462 14	18 U	1130	795
		6 462 15	21 U	1130	795
	removable side panels	6 462 50	6 U	985	1080
		6 462 51	9 U	985	1080
		6 462 52	12 U	985	1080
		6 462 53	15 U	985	1080
		6 462 54	18 U	985	1080
		6 462 55	21 U	985	1080
		6 462 60	6 U	1135	1080
		6 462 61	9 U	1135	1080
		6 462 62	12 U	1135	1080
		6 462 63	15 U	1135	1080
		6 462 64	18 U	1135	1080
		6 462 65	21 U	1135	1080
19" pivoting cabinets		6 462 21	9 U	1140	1080
		6 462 22	12 U	1140	1080
		6 462 23	15 U	1140	1080
		6 462 24	18 U	1140	1080
		6 462 25	21 U	1140	1080
10" fix cabinet		6 462 30	6 U	600	575

Linkeo 19" wall-mounting cabinets

Pivoting base opening




Fixing (mm)



		Cat.Nos	Capacity	X	Y
19" fix cabinet	fix side panels	6 462 00	6 U	400	197
		6 462 01	9 U	400	300
		6 462 02	12 U	400	464
		6 462 03	15 U	400	597
		6 462 04	18 U	400	730
		6 462 05	21 U	400	864
		6 462 10	6 U	400	197
		6 462 11	9 U	400	330
		6 462 12	12 U	400	464
		6 462 13	15 U	400	597
	removable side panels	6 462 14	18 U	400	730
		6 462 15	21 U	400	864
		6 462 50	6 U	411	149
		6 462 51	9 U	411	282
		6 462 52	12 U	411	415
		6 462 53	15 U	411	549
		6 462 54	18 U	411	682
		6 462 55	21 U	411	815
		6 462 60	6 U	411	149
		6 462 61	9 U	411	282
19" pivoting cabinets		6 462 62	12 U	411	415
		6 462 63	15 U	411	549
		6 462 64	18 U	411	682
		6 462 65	21 U	411	815
		6 462 21	9 U	350	368
10" fix cabinet		6 462 22	12 U	350	501
		6 462 23	15 U	350	635
		6 462 24	18 U	350	768
		6 462 25	21 U	350	901
		6 462 30	6 U	171	197

Fan kit (mm)




Bati-rack

■ Bati-rack general characteristics


Metal bati-rack
RAL 7035 textured polyester coating providing excellent resistance to corrosion and scratching
Perforations in 19" uprights: 9.5 x 9.5 mm
Permissible load: 300 kg

■ Dimensions (mm)

2-upright bati-rack Cat.No 0 463 95



4-upright bati-rack Cat.No 0 463 96



FOLLOW US
ALSO ON

@ legrand.com
 youtube.com/user/legrand
 facebook.com/Legrand
 twitter.com/Legrand
 pinterest.com/legrandgroup
 instagram.com/legrandnews



Headquarters

128, avenue de Lattre de Tassigny
87045 Limoges Cedex
France
Tel.: + 33 (0) 5 55 06 87 87
Fax: + 33 (0) 5 55 06 88 88